

1


2

3

4

ROHS

seal ring



3D View

5.00 [0.197]

1.40 [0.055]

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.09.22	

Specifications(规格):


- 1.Impedance(特性阻抗) : 50Ω;
- 2.Frequency (工作频率) : DC~6GHz;
- 3.VSWR (驻波比) : 1.50 @DC~3GHz;
- 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
- 5.Dielectric withstand voltage (介质耐电压) : 500V AC;
- 6.Mating cycles (耐久性) : ≥25 cycles;
- 7.Temperature range(使用温度): -40℃~+105℃;

PART NO.:

XS50AKMX-WZ04

Code: A~Z

30: H=3.0mm
35: H=3.5mm
50: H=5.0mm



6	Spring	Copper Alloy	Tin PLATED	1 PC	
5	Seal ring	Silicon rubber		1 PC	
4	Dielectric	PTFE		1 PC	
3	Outer Conductor-2	Copper Alloy	Ni PLATED	1 PC	
2	Outer Conductor-1	Zinc Alloy	Tin PLATED	1 PC	
1	Center Conductor	Copper Alloy	Gold PLATED	1 PC	
NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	Note

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn



DESIGN	希文	VIEW:
CHECKED		UNIT: mm/in
APPROVED		SIZE: A4

ANGULAR	±5°
X.	±0.50
X.x	±0.30
X.xx	±0.20
X.xxx	±0.10

UNSPECIFIED TOLERANCES

MODEL TYPE:

FAKRA (M) TO SMB (F) H=5.0mm

PART NO.:

XS50AKMX-WZ04

DWG NO.:

X-XS50AKMX-WZ04

SCALE	PAGE	REVISION
N/A	1/2	A0

XKB INDUSTRIAL PRECISION CO.,LIMITED

1

2

3

4

1












2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.09.22	

Code List:

Colde							
	A	B	C	D	E	F	G
Color/RAL-No.							
PART NO.	XS50AKMA-WZ04	XS50AKMB-WZ04	XS50AKMC-WZ04	XS50AKMD-WZ04	XS50AKME-WZ04	XS50AKMF-WZ04	XS50AKMG-WZ04
Colde							
	H	I	K	L	M	N	Z
Color/RAL-No.							
PART NO.	XS50AKMH-WZ04	XS50AKMI-WZ04	XS50AKMK-WZ04	XS50AKML-WZ04	XS50AKMM-WZ04	XS50AKMN-WZ04	XS50AKMZ-WZ04

NOTE: ALL RIGHTS RESERVED,BANNED COPY!

	DESIGN	希文	VIEW: 	MODEL TYPE: FAKRA (M) TO SMB (F) H=5.0mm		
	CHECKED		UNIT: mm/in	PART NO.: XS50AKMX-WZ04		
	APPROVED		SIZE: A4	DWG NO.: X-XS50AKMX-WZ04		
XKB INDUSTRIAL PRECISION CO.,LIMITED				SCALE N/A	PAGE 1/2	REVISION A0

1

2

3

4