







标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE




- NOTES:
- 1. FREQUENCY RANGE:
DC TO 6GHZ (VSWR: 1.3Max. AT 0.1~3GHZ,
1.4Max. AT 3~6GHZ)
 - 2. CHARACTERISTIC IMPEDANCE: 50Ω(NOMINAL);
 - 3. TEMPERATURE: -40℃ TO +90℃;
 - 4. RATED VOLTAGE : 60VAC;
 - 5. CONTACT RESISTANCE :
20mΩ Max.(SIGNAL CONTACT)
10mΩ Max.(GROUND CONTACT)
 - 6. WITHSTAND VOLTAGE : 200VAC FOR 1 MINUTE ;
 - 7. INSULATION RESISTANCE : 500MΩ Min. AT 100VDC;
 - 8.THE HARMFUL MATERIAL OF THIS PART SHOULD BE COMPLIANCE WITH CCT DOCUMENT QW-QA-10.



SIGNAL CONTACT GROUND CONTACT
P.C.B DIMENSION (TOP VIEW)
(TOLERRANCE ±0.05)

2	接触	铜合金	NI 50u"全镀层/AU 1u"全涂层	
1	基座	LCP	黑色	
序 号	品 名	材 质	电镀/颜色	备 注

 深圳市虹成电子有限公司		品 名 TITLE	连接器	
		料 号 PART NO	HC-IPEX0060-04	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	
X. ± 0.25	X. ° ± 2°	单 位 UNIT	MM	制 图 DRAW
.X ± 0.20	.X ° ± 1°	张 数 PART NO	1 OF 1	审 核 CHECKED
.XX ± 0.15	.XX ° ± 0.5°	版 本 REV	A	批 准 APPROVE
				夏操云
				赵亮亮

