


ROHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.09.20	

- Specifications(规格):
- 1.Impedance(特性阻抗) : 50Ω;
 - 2.Frequency (工作频率) : DC~6GHz;
 - 3.VSWR (电压驻波比) : 1.60 Max.;
 - 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
 - 5.Dielectric withstand voltage (介质耐电压) : 800V AC;
 - 6.Mating cycles (耐久性) : ≥25 cycles;
 - 7.Engagement force(啮合力) : ≤30N;
 - 8.Retention force latch(保持力) : ≥110N;
 - 9.Temperature range(使用温度): -40℃~+105℃;

PART NO.:
XM0RLF2S7-NA66-X
Code: A~Z



6	Outer Ferrule	Copper Alloy	Tin PLATED	2 PCS	5000PCS/R
5	Center Conductor	Copper Alloy	Gold PLATED	2 PCS	5000PCS/R
4	Dielectric	PBT		2 PCS	
3	Outer Conductor	Copper Alloy	Tin PLATED	2 PCS	
2	Housing	PBT		1 PC	
1	Secondary Lock	PBT		1 PC	
NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	Note

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn










XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	希文	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

ANGLAR	±5°
X.	±0.50
X.x	±0.30
X.xx	±0.20
X.xxx	±0.10
UNSPECIFIED TOLERANCES	
MODEL TYPE: Horizontal MINI FAKRA Female Connector for Dacar302. Double	
PART NO.: XM0RLF2S7-NA66-X	
DWG NO.: X-XM0RLF2S7-NA66-X	
SCALE	PAGE
N/A	1/2
REVISION	
A0	

Code List:

Colde							
	A	B	C	D	E	F	Z
Color/RAL-No.	Black/9005	White/9001	Blue/5005	Bordeaux/4004	Green/6002	Brown/8011	Water Blue/5021
PART NO.	XMORLF2S7-NA66-A	XMORLF2S7-NA66-B	XMORLF2S7-NA66-C	XMORLF2S7-NA66-D	XMORLF2S7-NA66-E	XMORLF2S7-NA66-F	XMORLF2S7-NA66-Z

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	希文	VIEW: 	MODEL TYPE: Horizontal MINI FAKRA Female Connector for Dacar302. Double		
CHECKED		UNIT: mm/in	PART NO.: XMORLF2S7-NA66-X		
APPROVED		SIZE: A4	DWG NO.: X-XMORLF2S7-NA66-X		
PRECISION CO.,LIMITED			SCALE	PAGE	REVISION
			N/A	2 / 2	A0

NOTE: ALL RIGHTS RESERVED,BANNED COPY!