

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

A

B

C

D

E

F

G

A

B



C

D

E





F

G



SCHEMATIC

- 3 (Ground PIN)
2 (SIGNAL PIN)



SIGNAL CONTACT GROUND CONTACT
P.C.B DIMENSION (TOP VIEW)
(TOLERRANCE ±0.05)

NOTES:

- FREQUENCY RANGE:
DC TO 6GHZ (VSWR: 1.3Max. AT 0.1~3GHZ,
1.4Max. AT 3~6GHZ)
- CHARACTERISTIC IMPEDANCE: 50Ω(NOMINAL);
- TEMPERATURE: -40°C TO +90°C;
- RATED VOLTAGE : 60VAC;
- CONTACT RESISTANCE :
20mΩ Max.(SIGNAL CONTACT)
10mΩ Max.(GROUND CONTACT)
- WITHSTAND VOLTAGE : 200VAC FOR 1 MINUTE ;
- INSULATION RESISTANCE : 500MΩ Min. AT 100VDC;
- THIS COMPONENT IS HALOGEN FREE.
- THE HARMFUL MATERIAL OF THIS PART SHOULD BE COMPLIANCE WITH CCT DOCUMENT QW-QA-10.

2	接触	铜合金	镀金/镀镍	
1	基座	LCP	黑色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	连接器
料号 PART NO	HC-IPEX0085-03

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X. ± 0.25	X. ° ± 2°	单 位 UNIT	MM	制 图 DRAW	AhYe
.X ± 0.20	.X ° ± 1°	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
.XX ± 0.15	.XX ° ± 0.5°	版 本 REV	A	批 准 APPROVE	赵亮亮

