









ROHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		Upgrade Drawing Frame	2024.11.12	
A2	N/A		Add Spare part: NUT and WASHER	2024.11.26	



3D View

- Specifications(规格):
- 1.Voltage rating(额定电压): 500V AC DC
 - 2.Withstanding voltage(耐压值): $\geq 1500V$ AC/minute;
 - 3.Insulation resistance(绝缘电阻): 1000MQ Min.;
 - 4.Temperature range(使用温度): $-20^{\circ}C \sim +85^{\circ}C$



9	NUT	Copper Alloy	Ni PLATED	2 PC	
8	WASHER	SPCC	Ni PLATED	2 PC	
7	CONTACT PIN	Copper Alloy	Gold PLATED	1 PC	
6	LEG	Copper Alloy	Tin PLATED	2 PCS	
5	SHORT CENTER CONTACT	Copper Alloy	Gold PLATED	1 PC	
4	BODY-2	Zinc Alloy	Ni PLATED	1 PC	
3	INSULATOR	POM/PP/PE/ABS		2/2/1/1PCS	
2	LONG CENTER CONTACT	Copper Alloy	Gold PLATED	1 PC	
1	BODY-1	Zinc Alloy	Ni PLATED	1 PC	
NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	NOTE



DESIGN	希文	VIEW:	MODEL TYPE: Double BNC R/A Connector
CHECKED		UNIT: mm/in	PART NO.: XBNWF7RD-2Z01
APPROVED		SIZE: A4	DWG NO.: X-XBNWF7RD-2Z01
XKB INDUSTRIAL PRECISION CO.,LIMITED			SCALE: N/A
			PAGE: 1/1
			REVISION: A2

ANGULAR	$\pm 5^{\circ}$
X.	± 0.50
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	