

1



2

3

4

ROHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.08.22	




3D View

- Specifications(规格):
- 1.Impedance(特性阻抗) : 50Ω;
 - 2.Frequency (工作频率) : DC~6GHz;
 - 3.VSWR (电压驻波比) : 1.50 @3GHz;
1.60 @6GHz;
 - 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
 - 5.Dielectric withstand voltage (介质耐电压) : 800V AC;
 - 6.Mating cycles (耐久性) : ≥25;
 - 7.Engagement force(啮合力) : ≤25N;
 - 8.Retention force latch(保持力) : ≥110N;
 - 9.Temperature range(使用温度): -40℃~+105℃;

PART NO.:
XK1PLF1S7-NA16-X


Code: A~Z

9.30 [0.366]




10.10 [0.398]

12.95 [0.510]



15.75 [0.620]

BOM List:



6	Outer Ferrule	Copper Alloy	Tin PLATED	1 PC	5000PCS/R
5	Dielectric	PBT		1 PC	
4	Outer Conductor	Copper Alloy	Tin PLATED	1 PC	
3	Center Conductor	Copper Alloy	Gold PLATED	1 PC	5000PCS/R
2	Housing	PBT		1 PC	
1	Secondary Lock	PBT		1 PC	
NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	Note

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn



DESIGN	希文	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

ANGULAR	±5°
X.	±0.50
X.x	±0.30
X.xx	±0.20
X.xxx	±0.10
UNSPECIFIED TOLERANCES	

MODEL TYPE: FAKRA Female Connector for 302		
PART NO.: XK1PLF1S7-NA16-X		
DWG NO.: X-XK1PLF1S7-NA16-X		

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/2	A0

1

2

3

4

1















2

3

4

REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	2024.08.22

Code List:

Colde							
	A	B	C	D	E	F	G
Color/RAL-No.	Black/9005	White/9001	Blue/5005	Bordeaux/4004	Green/6002	Brown/8011	Grey/7031
PART NO.	XK1PLF1S7-NA16-A	XK1PLF1S7-NA16-B	XK1PLF1S7-NA16-C	XK1PLF1S7-NA16-D	XK1PLF1S7-NA16-E	XK1PLF1S7-NA16-F	XK1PLF1S7-NA16-G
Colde							
	H	I	K	L	M	N	Z
Color/RAL-No.	Violet/4003	Beige/1001	Curry/1027	Carmine red/3002	Pastel Orange/2003	Pastel Green/6019	Water Blue/5021
PART NO.	XK1PLF1S7-NA16-H	XK1PLF1S7-NA16-I	XK1PLF1S7-NA16-K	XK1PLF1S7-NA16-L	XK1PLF1S7-NA16-M	XK1PLF1S7-NA16-N	XK1PLF1S7-NA16-Z

NOTE: ALL RIGHTS RESERVED,BANNED COPY!

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	希文	VIEW: 	MODEL TYPE: FAKRA Female Connector for 302
CHECKED		UNIT: mm/in	PART NO.: XK1PLF1S7-NA16-X
APPROVED		SIZE: A4	DWG NO.: X-XK1PLF1S7-NA16-X

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	2/2	A0

1

2

3

4