






ROHS



3D View



7.20 [0.283]
(2.00 [0.079])



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.09.18	

Specifications(规格):


- 1.Impedance(特性阻抗) : 100Ω;
- 2.Frequency (工作频率) : DC~2GHz;
- 3.Return Loss (回波损耗) : ≥ 20dB @1GHz;
- 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
- 5.Dielectric withstand voltage (介质耐电压) : 250V AC;
- 6.Mating cycles (耐久性) : ≥25 cycles;
- 7.Engagement force(啮合力) : ≤ 60N;
- 8.Retention force latch(保持力) : ≥110N;
- 9.Temperature range(使用温度): -40℃~+105℃;

PART NO.:

XH6PLF1R5-NL06-X

Code: A~Z

BOM List:



11	Outer Ferrule	Copper Alloy	Ni PLATED	1 PC	2KPCS/R
10	Cover	Copper Alloy	Ni PLATED	1 PC	
9	Center Conductor-2	Copper Alloy	Gold PLATED	2 PCS	5KPCS/R
8	Center Conductor-1	Copper Alloy	Gold PLATED	2 PCS	5KPCS/R
7	Power PIN	Copper Alloy	Tin PLATED	2 PCS	13KPCS/R
6	Secondary Lock-2	PA66		1 PC	
5	Dielectric-2	PA66		1 PC	
4	Dielectric-1	PA66		1 PC	
3	Outer Conductor	Zinc Alloy	Ni PLATED	1 SET	
2	Secondary Lock-1	SUS		1 PC	
1	Housing	PBT		1 PC	
NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	Note

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn



DESIGN	希文	VIEW:	MODEL TYPE: HSD4+2P Female R/A Connector
CHECKED		UNIT: mm/in	PART NO.: XH6PLF1R5-NL06-X
APPROVED		SIZE: A4	DWG NO.: X-XH6PLF1R5-NL06-X
			SCALE PAGE REVISION
			N/A 1/2 A0

XKB INDUSTRIAL PRECISION CO.,LIMITED

1








2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.09.18	

Code List:

Colde							
	A	B	C	D	E	F	Z
Color/RAL-No.	Black/9005	White/9001	Blue/5005	Bordeaux/4004	Green/6002	Brown/8011	Water Blue/5021
PART NO.	XH6PLF1R5-NL06-A	XH6PLF1R5-NL06-B	XH6PLF1R5-NL06-C	XH6PLF1R5-NL06-D	XH6PLF1R5-NL06-E	XH6PLF1R5-NL06-F	XH6PLF1R5-NL06-Z

NOTE: ALL RIGHTS RESERVED,BANNED COPY!

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	希文	VIEW: 	MODEL TYPE: HSD4+2P Female R/A Connector
CHECKED		UNIT: mm/in	PART NO.: XH6PLF1R5-NL06-X
APPROVED		SIZE: A4	DWG NO.: X-XH6PLF1R5-NL06-X
XKB INDUSTRIAL PRECISION CO.,LIMITED			SCALE N/A
			PAGE 2/2
			REVISION A0

1

2

3

4