



ROHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.09.22	






3D View

Specifications(规格):
1.Impedance(特性阻抗) : 50Ω;
2.Frequency (工作频率) : DC~6GHz;
3.Insulation resistance(绝缘阻抗) : ≥100MΩ;
4.Dielectric withstand voltage (介质耐电压) : 500V AC;
5.Mating cycles (耐久性) : ≥25 cycles;
6.Temperature range(使用温度): -40℃~+105℃;

PART NO.:
XS 50 LFS3 - WL14

30: H=3.0mm
35: H=3.5mm
50: H=5.0mm



8	Protective cover	PP		1 PC	
7	Crimp Sleeve	Copper Alloy	Ni PLATED	1 PC	
6	Spring	Copper Alloy	Tin PLATED	1 PC	
5	Seal ring	Silicon rubber		1 PC	
4	Dielectric	PTFE		1 PC	
3	Outer Conductor-2	Copper Alloy	Ni PLATED	1 PC	
2	Outer Conductor-1	Zinc Alloy	Tin PLATED	1 PC	
1	Center Conductor	Copper Alloy	Gold PLATED	1 PC	
NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	Note

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn



DESIGN	希文	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

ANGULAR	±5°
X.	±0.50
X.x	±0.30
X.xx	±0.20
X.xxx	±0.10

UNSPECIFIED TOLERANCES	
MODEL TYPE: SMB Female Connector, H=5.0mm	
PART NO.: XS50LFS3-WL14	
DWG NO.: X-XS50LFS3-WL14	

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A0