



ROHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.09.22	





3D View



- Specifications(规格):
- 1.Impedance(特性阻抗) : 50Ω;
 - 2.Frequency (工作频率) : DC~6GHz;
 - 3.VSWR (驻波比) : 1.50 @DC~3GHz;
 - 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
 - 5.Dielectric withstand voltage (介质耐电压) : 500V AC;
 - 6.Mating cycles (耐久性) : ≥25 cycles;
 - 7.Temperature range(使用温度): -40℃~+105℃;

PART NO.:
XS35A KMX-WZ04

Code: A~Z
30: H=3.0mm
35: H=3.5mm
50: H=5.0mm



6	Spring	Copper Alloy	Tin PLATED	1 PC	
5	Seal ring	Silicon rubber		1 PC	
4	Dielectric	PTFE		1 PC	
3	Outer Conductor-2	Copper Alloy	Ni PLATED	1 PC	
2	Outer Conductor-1	Zinc Alloy	Tin PLATED	1 PC	
1	Center Conductor	Copper Alloy	Gold PLATED	1 PC	
NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	Note

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

















DESIGN	希文	VIEW:
CHECKED		UNIT: mm/in
APPROVED		SIZE: A4

XKB INDUSTRIAL PRECISION CO.,LIMITED

ANGULAR	±5°	
X.	±0.50	
X.x	±0.30	
X.xx	±0.20	
X.xxx	±0.10	
UNSPECIFIED TOLERANCES		
MODEL TYPE: FAKRA (M) TO SMB (F) H=3.5mm		
PART NO.: XS35AKMX-WZ04		
DWG NO.: X-XS35AKMX-WZ04		
SCALE	PAGE	REVISION
N/A	1 / 2	A0

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.09.22	

Code List:							
Colde							
	A	B	C	D	E	F	G
Color/RAL-No.							
PART NO.	XS35AKMA-WZ04	XS35AKMB-WZ04	XS35AKMC-WZ04	XS35AKMD-WZ04	XS35AKME-WZ04	XS35AKMF-WZ04	XS35AKMG-WZ04
Colde							
	H	I	K	L	M	N	Z
Color/RAL-No.							
PART NO.	XS35AKMH-WZ04	XS35AKMI-WZ04	XS35AKMK-WZ04	XS35AKML-WZ04	XS35AKMM-WZ04	XS35AKMN-WZ04	XS35AKMZ-WZ04

NOTE: ALL RIGHTS RESERVED,BANNED COPY!

	DESIGN	希文	VIEW: 	MODEL TYPE: FAKRA (M) TO SMB (F) H=3.5mm		
	CHECKED		UNIT: mm/in	PART NO.: XS35AKMX-WZ04		
	APPROVED		SIZE: A4	DWG NO.: X-XS35AKMX-WZ04		
XKB INDUSTRIAL PRECISION CO.,LIMITED				SCALE N/A	PAGE 1/2	REVISION A0