



ROHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.08.22	

3D View

Specifications(规格):

- 1.Impedance(特性阻抗) : 50Ω;
- 2.Frequency (工作频率) : DC~6GHz;
- 3.VSWR (电压驻波比) : 1.50 @3GHz;
1.60 @6GHz;
- 4.Insulation resistance(绝缘阻抗) : $\geq 100\text{M}\Omega$;
- 5.Dielectric withstand voltage (介质耐电压) : 800V AC;
- 6.Mating cycles (耐久性) : ≥ 25 ;
- 7.Engagement force(啮合力) : $\leq 25\text{N}$;
- 8.Retention force latch(保持力) : $\geq 110\text{N}$;
- 9.Temperature range(使用温度) : $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$;

PART NO.:

XK1PLF1S3-NA16-X

Code: A~Z


9.30 [0.366]

10.10 [0.398]

12.95 [0.510]

<15.75 [0.620]>

BOM List:



6	Outer Ferrule	Copper Alloy	Tin PLATED	1 PC	5000PCS/R
5	Dielectric	PBT		1 PC	
4	Outer Conductor	Copper Alloy	Tin PLATED	1 PC	
3	Center Conductor	Copper Alloy	Gold PLATED	1 PC	5000PCS/R
2	Housing	PBT		1 PC	
1	Secondary Lock	PBT		1 PC	
NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	Note

www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn















XK13 星坤
Connection

DESIGN	希文	VIEW:	MODEL TYPE: FAKRA Female Connector for RG174
CHECKED		UNIT: mm/in	PART NO.: XK1PLF1S3-NA16-X
APPROVED		SIZE: A4	DWG NO.: X-XK1PLF1S3-NA16-X
			SCALE PAGE REVISION N/A 1/2 A0

XKB INDUSTRIAL PRECISION CO.,LIMITED

REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	2024.08.22

Code List:

Colde							
	A	B	C	D	E	F	G
Color/RAL-No.	Black/9005	White/9001	Blue/5005	Bordeaux/4004	Green/6002	Brown/8011	Grey/7031
PART NO.	XK1PLF1S3-NA16-A	XK1PLF1S3-NA16-B	XK1PLF1S3-NA16-C	XK1PLF1S3-NA16-D	XK1PLF1S3-NA16-E	XK1PLF1S3-NA16-F	XK1PLF1S3-NA16-G
Colde							
	H	I	K	L	M	N	Z
Color/RAL-No.	Violet/4003	Beige/1001	Curry/1027	Carmine red/3002	Pastel Orange/2003	Pastel Green/6019	Water Blue/5021
PART NO.	XK1PLF1S3-NA16-H	XK1PLF1S3-NA16-I	XK1PLF1S3-NA16-K	XK1PLF1S3-NA16-L	XK1PLF1S3-NA16-M	XK1PLF1S3-NA16-N	XK1PLF1S3-NA16-Z

NOTE: ALL RIGHTS RESERVED,BANNED COPY!

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	希文
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	FAKRA Female Connector for RG174
PART NO.:	XK1PLF1S3-NA16-X
DWG NO.:	X-XK1PLF1S3-NA16-X

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	2/2	A0