







ROHS



Recommended P.C.B Layout

ANGLAR	$\pm 5^\circ$
X.	± 0.50
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.10

UNSPECIFIED TOLERANCES

MODEL TYPE:
MINI FAKRA R/A Male ConnectorPART NO.:
XMORWM43-NC05-XDWG NO.:
X-XMORWM43-NC05-XSCALE PAGE REVISION
N/A 1/2 A0

4	Dielectric	LCP		4 PCS	
3	Outer Conductor	Zinc Alloy	Tin PLATED	1 PC	
2	Center Conductor	Copper Alloy	Gold PLATED	4 PCS	
1	Housing	PBT		1 PC	
NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	Note
		www.helloxkb.com	www.helloxkb.cn	www.xk-dq.cn	










XKB INDUSTRIAL PRECISION CO.,LIMITED

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.08.26	

Code List:

Colde							
A							
Color/RAL-No.	Black/9005	White/9010	Blue/5012	Bordeaux/4004	Green/6017	Brown/8011	Water Blue/5021
PART NO.	XMORWM43-NC05-A	XMORWM43-NC05-B	XMORWM43-NC05-C	XMORWM43-NC05-D	XMORWM43-NC05-E	XMORWM43-NC05-F	XMORWM43-NC05-Z

NOTE: ALL RIGHTS RESERVED, BANNED COPY!

ANGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN

希文

VIEW:

MODEL TYPE:
MINI FAKRA R/A Male Connector

CHECKED

UNIT: mm/in

PART NO.:
XMORWM43-NC05-X

APPROVED

SIZE: A4

DWG NO.:
X-XMORWM43-NC05-X