



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~ +85℃
- 4、Contact Resistance: 10mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Housing PA66 UL94-V0

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	HC-XHB-2Y-X	2.50	5.70	3.00
3	HC-XHB-3Y-X	5.00	8.20	4.00
4	HC-XHB-4Y-X	7.50	10.70	5.00
5	HC-XHB-5Y-X	10.00	13.20	7.50
6	HC-XHB-6Y-X	12.50	15.70	10.00
7	HC-XHB-7Y-X	15.00	18.20	
8	HC-XHB-8Y-X	17.50	20.70	
9	HC-XHB-9Y-X	20.00	23.20	
10	HC-XHB-10Y-X	22.50	25.70	
11	HC-XHB-11Y-X	25.00	28.20	
12	HC-XHB-12Y-X	27.50	30.70	
13	HC-XHB-13Y-X	30.00	33.20	12.50
14	HC-XHB-14Y-X	32.50	35.70	
15	HC-XHB-15Y-X	35.00	38.20	
16	HC-XHB-16Y-X	37.50	40.70	
17	HC-XHB-17Y-X	40.00	43.20	
18	HC-XHB-18Y-X	42.50	45.70	
19	HC-XHB-19Y-X	45.00	48.20	
20	HC-XHB-20Y-X	47.50	50.70	

Ordering Information

HC-XHB - N*** - *

Pin: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20

Title: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20

Colour: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20

		GENERAL TOLERANCE		制图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
		DIM	TOL	审核				
		X.X	±0.30	检查	产品名称	XHB (2.50)单排带扣孔座	版本	A
		X.XX	±0.20	批准	产品料号	HC-XHB-NY-X	单位	mm
		X.XXX	±0.10	比例	材料		页次	1/1
序号	变更内容	日期	投影	投影				
No.	MODIFY CONTENT	MODIFY DATE	Angle ±3.0°	Projection				