






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		料号变更图面升级整理图面	2024.11.24	阿树



■SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating:3A AC/DC
- Withstanding Voltage:800V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤10mΩ
- After environmental testing:≤20mΩ

PART NO.:

X2000 H M-XX A-N0
① ② ③ ④ ⑤ ⑥

- ①Series No
②Category:H-HSG
③Category:M-Male Housing
④Row No.Pin No:XX-02~16P
⑤A:WITH OUT With Snap Joint
⑥Material:N0-PA66 UL94V-0

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	4.34	6.10	10	18.00	20.34	22.10
03	4.00	6.34	8.10	11	20.00	22.34	24.10
04	6.00	8.34	10.10	12	22.00	24.34	26.10
05	8.00	10.34	12.10	13	24.00	26.34	28.10
06	10.00	12.34	14.10	14	26.00	28.34	30.10
07	12.00	14.34	16.10	15	28.00	30.34	32.10
08	14.00	16.34	18.10	16	30.00	32.34	34.10
09	16.00	18.34	20.10				

X2000HM-XXA-N0	PA66 UL 94V-0	X2000T	X2000W
PART NO	Matrial	Suitable XKB Terminal	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuces	



DESIGN	阿树	VIEW:		MODEL TYPE: 2.00mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.: X2000HM-XXA-N0
APPROVED		SIZE:	A4	DWG NO.: