


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		系列号变更，图面升级整理图面	2024.11.24	阿树




Specification:
Volatage Rating:250V AC/DC
Current Rating :3A AC/DC
Withstaning Voltage:800V AC/Minute
Temperature Range:-40°~+125°
Insulation Resistance:≥1000MΩ
Contact Resistance:≤10MΩ


PART NO.:

X2000 T F-X X XX-X
① ② ③ ④ ⑤ ⑥ ⑦


- ①Series Number.
②Category: T-terminal
③Welding Board Angle:F-Female Terminal
④Material:P-Phosphor Bronze
H-High Conductivity Copper
⑤Plating Code:SN:40~120u"(1~3um)Ni
80~200u"(2~5um)Tin
SN1:40~120u"(1~3um)Tin
⑥Plating Process:S-Stamping before Plating
P-Stamping after Plating
⑦Barrel type:H-High Feet; L-Low Feet



SECTION:A-A
SCALE:1:1



SECTION:B-B
SCALE:1:1



	X2000TF-XXXX-X	Phosphor Bronze	X2000HM	X2000W
	PART NO	Material	Suitable XKB Housing	Suitable XKB Wafer
X2000TF-XXXX-H	AWG#22-20 (0.35~0.5mm ²)	ø1.6mm Max	1.80	1.70
X2000TF-XXXX-L	AWG#24-22 (0.22~0.35mm ²)		1.70	1.60
				X2000HM
PART NO	Wire Range	Insulation O.D	DIM A	DIM B
				Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 2.0mm Automobile connector
CHECKED		UNIT: mm/in	PART NO.: X2000TF-XXXX-X
APPROVED		SIZE: A4	DWG NO.: