



P . C . B LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃--+105℃

温度范围: -40℃--+105℃

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2001 W V - 2xXX A - 6T V01

① ② ③ ④ ⑤ ⑥ ⑦

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:V-Straight 180°

4.Row No.Pin No: 2xXX-2x03-2x32P

5.Category:A-No gap

6.Material:6T-Nylon 6T UL94V-0

7.Plating:V01-Gold Flash

Poles	Dimensions		Poles	Dimensions	
	A	B		A	B
2x03	4.00	13.30	2x12	22.00	31.30
2x04	6.00	15.30	2x13	24.00	33.30
2x05	8.00	17.30	2x15	28.00	37.30
2x06	10.00	19.30	2x17	32.00	41.30
2x07	12.00	21.30	2x20	38.00	47.30
2x08	14.00	23.30	2x22	42.00	51.30
2x09	16.00	25.30	2x25	48.00	57.30
2x10	18.00	27.30	2x30	58.00	67.30
2x11	20.00	29.30	2x32	62.00	71.30

X2001WV-2xXXA-6TV01	Nylon 6T	Brass	X2001H / X2001H2
PART NO	Material	Material(Pin)	Suitable XKB IDC

广东星坤科技股份有限公司	
生	日期
教	日期
MARK	DESCRIPTION
文件工程章	

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ANGLAR	±5°			
L≤ 4	±0.2			
4<L≤ 16	±0.3			
16<L≤ 63	±0.4			
L> 63	±0.5			

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW: ④	2.0mm Crimp Style Connector
CHKD	UNIT: mm/in	PART NO.:
APPD	SIZE: A4	X2001WV-2xXXA-6TV01
XKB INDUSTRIAL PRECISION CO.,LIMITED		DWG NO.:
		X-X2001WV-2xXXA-6TV01
WEIGHT	SHEET	REVISION
	1/1	A0