





1. 产品尺寸图Product Dimension Drawing



2. 产品电器参数Product electrical parameters

防护等级 (Ingress protection)	IP50
插拔测试 (Plugging and unplugging test)	<500次
产品耐温 (The product is temperature resistant)	-20° C / +85° C
盐雾腐蚀 (Salt Spray Corrosion)	>48 hr
额定电流Current rating	5A
额定电压 (Rated voltage)	125V
工作电压 (AC.V) Operating voltage (AC.V)	200
耐电压 (AC.V) Withstand voltage (AC.V)	1500
绝缘阻抗 (mΩ) DC500V Insulation Resistance (mΩ)DC500V	1500
绝缘电阻 (mΩ) DC1A Insulation Resistance (mΩ)DC1A	5

3. 环境及表面处理产品特性Environmental and surface treatment product characteristics

外壳材料 Housing material	锌合金镀镍Zinc alloy nickel plating
绝缘体材料 Insulator material	橡胶黑木Rubber black wood
触体材料 Contact material	黄铜镀银Brass silver-plated

1: 连接器组装生产所有公差通常为0.1mm,2: 插座直接拧入螺纹孔中, 螺纹 +0.05mm 1: All tolerances are usually 0.1mm for connector assembly production, 2: The socket is screwed directly into the threaded hole, the thread is +0.05mm		东莞市通瑞电子科技有限公司 TongRuiJoin Dongguan Tongrui Electronic Technology Co., Ltd www.Cltfre.com	单芯图纸Single-core drawings	
			单位unit:mm	修改revise:A0
		GX12弯针板接插座GX12 curved pin board socket	视图view: 	
			型号Model AD. GZ. GX12. 304. NYLV	