


1. 产品尺寸图Product Dimension Drawing



2. 产品电器参数Product electrical parameters

|                                             |                 |
|---------------------------------------------|-----------------|
| 防护等级 (Ingress protection)                   | IP50            |
| 插拔测试 (Plugging and unplugging test)         | <500次           |
| 产品耐温 (The product is temperature resistant) | -20° C / +85° C |
| 盐雾腐蚀 (Salt Spray Corrosion)                 | >48 hr          |
| 额定电流Current rating                          | 10A             |
| 额定电压 (Rated voltage)                        | 150V            |
| 工作电压 (AC.V)                                 | 400             |
| Operating voltage (AC.V)                    |                 |
| 耐电压 (AC.V)                                  | 1500            |
| Withstand voltage (AC.V)                    |                 |
| 绝缘阻抗 (mΩ ) DC500V                           | 2000            |
| Insulation Resistance (mΩ )DC500V           |                 |
| 绝缘电阻 (mΩ ) DC1A                             | 10              |
| Insulation Resistance (mΩ )DC1A             |                 |

3. 环境及表面处理产品特性Environmental and surface treatment product characteristics

|                          |                                |
|--------------------------|--------------------------------|
| 外壳材料 Housing material    | 锌合金镀镍Zinc alloy nickel plating |
| 绝缘体材料 Insulator material | 橡胶黑木Rubber black wood          |
| 触体材料 Contact material    | 黄铜镀银Brass silver-plated        |

1: 连接器组装生产所有公差通常为0.1mm,2: 插座直接拧入螺纹孔中, 螺纹 +0.05mm  
1: All tolerances are usually 0.1mm for connector assembly production, 2: The socket is screwed directly into the threaded hole, the thread is +0.05mm

TONGRUIJOIN

|                                                                                                   |                                   |             |
|---------------------------------------------------------------------------------------------------|-----------------------------------|-------------|
| 东莞市通瑞电子科技有限公司<br>TongRuiJoin<br>Dongguan Tongrui Electronic Technology Co., Ltd<br>www.CLtfre.com | 单芯图纸Single-core drawings          |             |
|                                                                                                   | 单位unit:mm                         | 修改revise:A0 |
|                                                                                                   | 视图view:                           |             |
| GX12弯针板插座GX12<br>curved pin board socket                                                          | 型号Model<br>AD. MT. GX20. 302. NYA |             |