

Ordering Information

备注(Remark)

1. 材料 (MATERIAL)

胶芯: PBT+30%G.F UL94V-0, 颜色:黑色.

Housing:PBT+30%G. F UL94V-0, Color:Black

四方针：黄铜，镍底30u"，表面镀金3u"

Contact:Brass, 3u" GOLD PLATING OVER ALL

30u" NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Raring Current:3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.

温度范围: -40°C to $+105^{\circ}\text{C}$

Temperture Range: -40° C to+105° C



HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Full Circle	Plating Solder	INSULATOR MATERIAL:	LENGTH OF TERMINAL	PACKING A: PE Bag B: Tape & Seal C: Tube D: Tube+CAP E: Tray
15: 1.5mm	2-40P	A0=0.80"	B0=0.8U	A: PBT		
17: 1.7mm		A1=1.0"	B1=1.0U	B: PA6T		
20: 2.0mm		A2=1.50"	B2=1.5U	C: PA9T		
25: 2.54mm		A3=2.0"	B3=2.0U	D: LCP		
30: 3.0mm		A4=3.0"	B4=3.0U			
		A5=5.0"	B5=5.0U			
		A6=10.0"	B6=10.0U			
		A7=15.0"	B7=15.0U			
		A8=20.0"	B8=20.0U			
		A9=30.0"	B9=30.0U			
		S1=Ordinary Tin Plated				
		S2= Matte Tin Plated				
		S3= Tin-plated High-temperature				

				OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.							
				X.X	±0.25	UNIT		MM									
				X.XX	±0.20	SIZE		A4		DESIGN		赵文品2025.03.05		PART NO.		P125-1206A4AS138A1	
				X.XXX	±0.10												
				Angle	±3°	SHEET		1/1		CHECK				TITLE:		2.54排针 2*6P L=13.8/3.0 180度 打内K PBT 镀3U金 500个/袋	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION		DIM	TOL		PROJ.				APPROVE				Customer No.	