







PCB. WELDING DRAWING



CIRCUIT DIAGRAM

Specification

Operating Life	300,000
Contact rating	50mA@12V DC.
Insulation resistance	100MΩ min.
Contact resistance	100mΩ max. initial.
Dielectric Strength	250 V AC(1mn)
Travel	0.35±0.2mm
Storage Temperature	-30° C to 80° C

Mechanical

ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR
E	Button	Silica	1	Pickling
D	COVER	Stainless Steel	1	Cleaning
C	DOME	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black
A	PIN	PHOSPHOR BRONZE	1	Plated Ag

Type	Force (gf) Operatin g	Height mm	Button	Leads Shape (G, J, T)	Ground pin (0, 1)	Pegs Option (0, 1)
YTS2K008	5	350gf±50	H	5.5	E (Ecru) U (Bale) W (White)	J
	4	400gf±50	I	5.0		
			G	5.2		
	3	250gf±50	F	4.8		
			E	4.5		
	2	160gf±50	D	4.3		
			C	3.8	0 (None)	0 (None)
	1	100gf±50	B	3.5		
			A	3.1		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD
Email at info@yiyuanswitches.com

UNITS mm
MAT'L
FINISH
Q'TY



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO.
YTS2K008
APPD: ROGER
CHKD: RDC
DR: BILLY WANG 2020/08/21

TITLE:
TACTILE SWITCH 6.2*6.2 触摸开关
DWG NO.:
YTS2K008
SCALE SHEET REV.
1/1 1/1 A1

Packaging:
Reel of 1,500 pieces for 3.1~3.5H
Reel of 1,000 pieces for 4.3~5.5H