







P.C.B LAYOUT(Top view)



Model No.	DC-044A-20A	DC-044A-25A
PIN	ø2.0	ø2.5

Rating:DC 30V 5A
 Contact Resistance:100 mΩ Max.
 Operating temperature:-30℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

④	Leaf spring	—	1	Phosphor bronze	Ag Plating	—
③	PIN	—	1	H65 Brass	Sn Plating	—
②	Terminal	—	3	H62 Brass	Ag Plating	—
①	Housing	—	1	PBT	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		 hro®	
DRAWN		LIUCAN	2021.12.8			
CHECKED				TITLE:	PHONE JACKS	
APPROVALS				PART NO.	DC-044A	
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20			
		5~10	±0.15			
		~ 5	±0.10			
		±2°		DRAWING NO.		PROJ: 
						SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.