


# MALE PCB PINS

## SOLDER TERMINALS SLOTTED

### 2315

2315-X-01-XX-00-00-07-0

Swage mount in 1,70 hole




| Basic Part Number | Board Thickness | Length V | Depth D |
|-------------------|-----------------|----------|---------|
| 2315-1            | 0,79            | 1,14     | 1,02    |
| 2315-2            | 1,57            | 2,39     | 1,57    |
| 2315-3            | 2,39            | 3,18     | 1,57    |
| 2315-4            | 3,18            | 3,96     | 1,57    |

### 2302

2302-X-01-XX-00-00-07-0

Swage mount in 1,70 hole




| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 2302-1            | 0,79            | 1,35     |
| 2302-2            | 1,57            | 2,13     |
| 2302-3            | 2,39            | 2,92     |
| 2302-4            | 3,18            | 3,73     |

### 2352

2352-X-01-XX-00-00-07-0

Swage mount in 1,70 hole




| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 2352-1            | 0,79            | 1,14     |
| 2352-2            | 1,57            | 2,39     |
| 2352-3            | 2,39            | 3,18     |
| 2352-4            | 3,18            | 3,96     |

### 2362

2362-X-01-XX-00-00-07-0

Swage mount in 1,70 hole




| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 2362-5            | 0,41            | 0,94     |
| 2362-1            | 0,79            | 1,35     |
| 2362-2            | 1,57            | 2,13     |
| 2362-3            | 2,39            | 2,92     |
| 2362-4            | 3,18            | 3,73     |

### 2507

2507-X-01-XX-00-00-07-0


Swage mount in 1,70 hole



### 2526

2526-X-01-XX-00-00-07-0

Swage mount in 1,63 hole



| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 25XX-1            | 0,79            | 1,35     |
| 25XX-2            | 1,57            | 2,13     |
| 25XX-3            | 2,39            | 2,92     |
| 25XX-4            | 3,18            | 3,73     |

#### SPECIFICATIONS:

**Pin Material:** Brass Alloy 360, 1/2 Hard  
(Swage pins are annealed)

**Dimensions:** Millimeters

**Tolerances On:** Lengths:  $\pm 0,13$   
Diameters:  $\pm 0,051$   
Angles:  $\pm 2^\circ$



ORDER CODE: XXXX - X - 01 - XX - 00 - 00 - 07 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 44 7,62μm SILVER OVER COPPER (RoHS)
- 50 7,62μm ELECTRO-SOLDER (60/40 SnPb)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com