

0359 0359-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole	0358 0358-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole	0360 0360-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole	0343 0343-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole
0356 0356-0-15-XX-34-XX-10-0 Solder mount in .102 min. mounting hole	6659 6659-0-15-XX-34-XX-10-0 Solder mount in .102 min. mounting hole	0347 0347-0-15-XX-34-XX-10-0 Solder mount in .120 min. mounting hole	0329 0329-0-15-XX-34-XX-10-0 Solder mount in .075 min. mounting hole. "knock out" bottom.
0814 0814-0-15-XX-34-XX-04-0 Solder mount in .082 min. mounting hole	5059 5059-0-15-XX-34-XX-04-0 Press-fit in .090 mounting hole	8360 8360-0-15-XX-34-XX-10-0 Press-fit in .087 mounting hole	9359 9359-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
 LENGTHS: ±.005
 DIAMETERS: ±.002
 ANGLES: ± 2°

ORDER CODE: XXXX - 0 - 15 - XX - 34 - XX - XX - 0

BASIC PART #
SPECIFY SHELL FINISH:
01 100μ" TIN/LEAD OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
01 200μ" TIN/LEAD OVER NICKEL
14 10μ" GOLD OVER NICKEL
27 30μ" GOLD OVER NICKEL

CONTACT

#34 CONTACT (DATA ON PAGE 212)