




- 1 PHENOLIC PER MIL-M-14, TYPE CFG, BLACK.
- 2 MATES WITH BLOCK 200277.
3. ACCOMODATES TYPE II #20 PIN CONTACTS.
- 4 $5.54^{+0.13}_0$ $\left[.218^{+.005}_{-.000} \right]$ WHEN USING JACKSCREWS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN B. CARBO	23 JUL 97	AMP AMP Incorporated Harrisburg, PA 17105-3608	
		CHK R. STONE	06 AUG 97		
DIMENSIONS, mm (INCHES)		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROVED G. STEINHAUER	NAME
		0 PLC ±-		PRODUCT SPEC	BLOCK, MALE, 50 POSITION, MINIATURE, RECTANGULAR M SERIES
		1 PLC ±-		APPLICATION SPEC	
		2 PLC ±0.13 (.005)		RESTRICTED TO	
		3 PLC ±-		SIZE	CAGE CODE
		4 PLC ±-		WEIGHT	DRAWING NO
		ANGLES ±-		A1 00779 ©=200276	
		FINISH -		CUSTOMER DRAWING	
				SCALE	3:1
				SHEET	1 OF 1
				REV	AK