





SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



N = Number of poles
Dim A=Nx5.08+1.0
Dim B=(N-1)x5.08
Dim C=Nx5.08+2.1

	Dim A	Dim B	Dim C
2-6p	±0.10	±0.15	±0.15
7-12p	±0.20	±0.20	±0.20
13-16p	±0.30	±0.25	±0.25
17-24p	±0.40	±0.35	±0.35

Material:

- Item :Terminal housing:Thermoplastic (UL94 V-0)

Electrical (Match with AR series)

- Voltage rating: 300V
- Current rating: 10A
- Wire range: 1.5~2.5mm²
- Withstanding Voltage: 1.6KV

KV xx 50 x 0 xxxx G

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

G: Pb<40000ppm
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KV 5.08 SERIES (With Hook & Low profile)						
PART NO.	KVxx50x0xxxxG			DWG NO.	8KV0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Kind	Kind		UNIT: mm		X. ±0.50
		2009.12.15	2009.08.10		SCALE: 2/1		X.X ±0.30
					SHEET: 01/01		X.XX ±0.10
					REV.: B		X° ±1°