

M85528/1 Mounting Flange, Full Perimeter

M85528/1-10 A

Basic Part No. _____ A = Primer Coat
Required

Shell Size _____

Note: part superceded by M85049/94




TABLE I

Shell Size	Thread UNJC-3B	A		B		C		D	
		±.003	(.1)	±.015	(.4)	-.010	(.3)	±.030	(.8)
8	4-40	.594	(15.1)	.880	(22.4)	.570	(14.5)	.136	(3.5)
10	4-40	.719	(18.3)	1.005	(25.5)	.700	(17.8)	.136	(3.5)
12	4-40	.812	(20.6)	1.098	(27.9)	.820	(20.8)	.136	(3.5)
14	4-40	.906	(23.0)	1.192	(30.3)	.945	(24.0)	.136	(3.5)
16	4-40	.969	(24.6)	1.255	(31.9)	1.070	(27.2)	.136	(3.5)
18	4-40	1.062	(27.0)	1.348	(34.2)	1.196	(30.4)	.136	(3.5)
20	4-40	1.156	(29.4)	1.500	(38.1)	1.320	(33.5)	.136	(3.5)
22	4-40	1.250	(31.8)	1.625	(41.3)	1.440	(36.6)	.136	(3.5)
24	6-32	1.375	(34.9)	1.750	(44.5)	1.570	(39.9)	.153	(3.9)
25	6-32	1.500	(38.1)	1.891	(48.0)	1.658	(42.1)	.153	(3.9)

1. For complete dimensions see applicable Military Specification.
2. Metric dimensions (mm) are indicated in parentheses.