



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE31670033	2016-06-14	Tom_Gu	Change Part No. of Half Finished



Conn.

△ CC-02AFMM-QL8W0P
Color: Black


White Printing
白色印刷



CC-02AFMM-QL8EXX

XX: 01~99Meters
01: 01Meter
02: 02Meters
...
99: 99Meters

- △ Note:
- * Important Dimension To Check.
 - * Working Voltage Rating: 300V AC
 - * Working Current Rating: Max. 20A
 - * Waterproof Rate: IP68.(Mated)
in 1 meter water within 24 hours
 - * Connector: Nylon+GF, Black.
 - * Male Pin: Copper Alloy, Gold Plated.
 - * Lock Nut: Nylon+GF, Black.
 - * Cable: SJTW 12WG*2C, Black,
PVC Jacket, OD=10.7mm.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View

2	White	白
1	Black	黑
Conn.	Wire Color	
	Pin Out	

UNIT:mm				TITLE		X Lok C-Size		ITEM NO		DRAWN BY		DATE	
TOLERANCE		±0.5		Cable 2 Pin 20A F Conn. M Pin				CC-02AFMM-QL8EXX		Tom_Gu		2016-06-14	
		SCALE		1:1		SIZE		A4		CHECKED BY		DATE	
		REV.		B		WC-REV.		A.1		Spring_Liu		2016-06-14	
								QC: Inspection item		CUSTOMER		DATE	
										ALTW		Kevin_Hu	

Amphenol LTW
安費諾亮泰企業股份有限公司