

## IE-BP-VAPP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



For protecting your devices against dust and dirt.

### General ordering data

|            |                                        |
|------------|----------------------------------------|
| Version    | Flange-mounted housing, protective cap |
| Order No.  | <a href="#">1068930000</a>             |
| Type       | IE-BP-VAPP                             |
| GTIN (EAN) | 4032248823093                          |
| Qty.       | 10 pc(s).                              |

## IE-BP-VAPP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                |            |
|------------|---------|----------------|------------|
| Depth      | 19.5 mm | Depth (inches) | 0.768 inch |
| Net weight | 11 g    |                |            |

## Temperatures

|                       |                |
|-----------------------|----------------|
| Operating temperature | -40 °C...70 °C |
|-----------------------|----------------|

## General data

|                  |              |                           |      |
|------------------|--------------|---------------------------|------|
| Colour           | black        | Protection degree         | IP54 |
| Type of mounting | Indoors only | UL 94 flammability rating | V-0  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002314    | ETIM 7.0    | EC002314    |
| ETIM 8.0    | EC002314    | ECLASS 9.0  | 27-44-02-08 |
| ECLASS 9.1  | 27-44-02-08 | ECLASS 10.0 | 27-44-02-08 |
| ECLASS 11.0 | 27-44-02-08 | ECLASS 12.0 | 27-44-02-08 |

## Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                    |                                                                                                                       |
|--------------------|-----------------------------------------------------------------------------------------------------------------------|
| Engineering Data   | <a href="#">WSCAD</a>                                                                                                 |
| User Documentation | <a href="#">MAN IE GUIDE DE</a><br><a href="#">MAN IE GUIDE EN</a>                                                    |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>                                                                              |
| Brochures          | <a href="#">FL FIELDWIRING EN</a><br><a href="#">PI PROFINET CABLING EN</a><br><a href="#">PI PROFINET CABLING EN</a> |

## IE-BP-VAPP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

