

MULTI-STRIPAX PV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

General ordering data

Version	Photovoltaics, Plug-in connector
Order No.	1190490000
Type	MULTI-STRIPAX PV
GTIN (EAN)	4032248973262
Qty.	1 pc(s).

MULTI-STRIPAX PV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	40 mm	Depth (inches)	1.575 inch
Height	85 mm	Height (inches)	3.346 inch
Width	250 mm	Width (inches)	9.842 inch
Net weight	548 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1	SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141
------------	----------------	------	--------------------------------------

Technical data

Description of article	Wire stripper unit
------------------------	--------------------

Stripping tools

Cable type	Photovoltaic cables and similar earthing cables and short-circuit-proof cables	Conductor cross-section (cutting capacity)	6 mm ²
Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	2.5 mm ²
Stripping length, min.	2 mm		

Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ECLASS 9.0	21-04-37-06
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-37-06
ECLASS 11.0	21-04-37-06	ECLASS 12.0	21-04-37-06

Approvals

Approvals



Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	