



Quality Products. Service Excellence.

R.F. Chokes 1537 Series
High Current

Features

- Large ferrite core for extended saturation point, optimum frequency range .01-2 Mhz.
- 1.5" long leads (+/- 0.1")
- Test frequency 1 Khz.
- Core length 1.25"
- Coil is covered with vinyl insulation shrink sleeve.
- Operating Temperature -55 degrees C to + 135 degrees C



Part No.	Inductance	Minimum Q	D.C. Resistance (Ohms)	Maximum D.C. Current (Amps)	Coil Diameter	Lead Diameter Gauge
	+/-5% (uH)					
1537E	10	4.5	0.006	20	0.63	14
1537F	20	6.5	0.013	12.5	0.60	16
1537G	30	5.3	0.024	8	0.58	18
1537H	40	5.2	0.039	5	0.57	20
1537J	50	3.4	0.064	3.2	0.56	20
1537K	75	3.2	0.128	2	0.54	20
1537L	100	10.5	0.05	8	0.71	18
1537M	250	12	0.114	5	0.69	18
1537N	500	11.6	0.26	3.2	0.65	20
1537P	750	10	0.465	2	0.61	20
1537R	1000	7.4	0.83	1.25	0.59	20

Tags: choke, high frequency, ferrite core, saturation, frequency

Data subject to change without notice