




SECTION P-P



SECTION F-F



Dimension

N= Number of poles

Dimension		Poles	Tolerance
Dim A	$N \times 7.5 + 1.50$	2P-6P	± 0.20
Dim B	$N \times 7.5$	7P-11P	± 0.30
Dim C	$(N-1) \times 7.5$	12P-16P	± 0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	10/30`13	add the dimensional label	Chen Bo
△	10/30`13	add the view	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ① Female contact: PhBz(CuSn), Tin plated
- Item ② Terminal Cover: Thermoplastic (UL94V-0)
- Item ③ Terminal housing: Thermoplastic (UL94V-0)
- Item ④ Terminal housing (B type): Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Critical dimension: △

KF xx A0 x 0 xxxx G

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
...
16 16 CONTACTS

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange (RAL2011/P)
- 4 Yellow (RAL1018/A)
- 5 Green (RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey (RAL7035/D)
- 9 White (RAL1102)
- C Green (RAL6018/U)

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KF 7.5 Series							
PART NO.	KFxxA0x0xxxxG				DWG NO.	8KF0401		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance
		Chen Bo 10/30`13	Chen Bo 10/30`13		UNIT: mm			X. ±0.5
					SCALE: NONE			X.X ±0.3
				SHEET: 01/01	REV.: C			X.XX ±0.1
								X° ±1°