





STRAIN RELIEF CLAMP  
2-TOTAL

| DIMENSIONS(mm/in) |         |         |         |         |         |
|-------------------|---------|---------|---------|---------|---------|
| SIZE              | A±0.3mm | B±0.5mm | C±0.5mm | D±0.3mm | E±0.3mm |
| 09                | 2.80    | 16.50   | 11.08   | 5.80    | 8.70    |
|                   | 0.110   | 0.649   | 0.436   | 0.228   | 0.342   |
| 15                | 2.80    | 19.20   | 13.14   | 5.80    | 8.70    |
|                   | 0.110   | 0.755   | 0.517   | 0.228   | 0.342   |
| 25                | 3.90    | 26.60   | 19.88   | 6.40    | 8.70    |
|                   | 0.153   | 1.047   | 0.783   | 0.251   | 0.342   |
| 37                | 3.80    | 26.60   | 19.88   | 6.40    | 13.00   |
|                   | 0.153   | 1.047   | 0.783   | 0.251   | 0.511   |
| 50                | 4.30    | 30.40   | 22.22   | 7.30    | 8.70    |
|                   | 0.169   | 1.196   | 0.875   | 0.287   | 0.342   |

MATERIAL: STEEL, NICKEL PLATED



STRAIN RELIEF SCREWS  
2-TOTAL

**GPHYYSRKIT**

SERIES \_\_\_\_\_  
POSITIONS \_\_\_\_\_

09  
15  
25  
37  
50

RoHS COMPLIANT

|  |                                                                                                                                                                                             |                            |
|--|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|
|  | THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. | DRAWN:<br><b>J. KADEL</b>  |
|  |                                                                                                                                                                                             | DATE:<br><b>03/08/2019</b> |

UNITS = inches [mm]

DO NOT SCALE FROM DRAWING

|                |                           |            |         |          |
|----------------|---------------------------|------------|---------|----------|
| <b>NorComp</b> | SCALE:<br>NTS             | SHEET<br>1 | OF<br>1 | REV<br>1 |
|                | DWG NO. <b>GPHYYSRKIT</b> |            |         |          |