





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
L	2	REVISED PER ECO-16-004800	10SEP2016	NK	MZ
M		REVISED PER ECO-16-018356	22MAR2017	RS	MZ
N		REVISED PER ECO-19-004839	03APR2019	RS	MZ
P		REVISED PER ECO-19-011232	08AUG2019	RS	MZ




DETAIL V
SCALE 20:1

- 1 HOUSING: NYLON, UL 94 V-0 RATED, COLOR: BLACK.
- 2 CONTACT:
BODY - BRASS, .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
- 3 CONTACT:
BODY - BRASS, .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
POST - BRASS, .000030 MIN GOLD OVER .000050 MIN NICKEL.
- 4 CONTACT:
BODY - BRASS, .000030 MIN GOLD OVER .000030 MIN NICKEL.
POST - BRASS, .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
- 5 CONTACT:
BODY - BRASS, .000100 MIN TIN OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN OVER .000050 MIN NICKEL.
- 6 PERIPHERAL SEAL - ELASTOMER, COLOR: BLACK.
- 7 .009 MAXIMUM CONTACT LEAD-IN SEAM GAP PERMISSIBLE ON MATING FACE END.
- 8 OBSOLETE PARTS: OBSOLETE C'S STREAMLINING PER D.RENAUD/D.SINISI

	.368	5	YES	ALL	213827-8
OBSOLETE	.368	5	YES	1-8, 10-19	213827-7
OBSOLETE	.368	2	NO	ALL	213827-6
8	OBSOLETE	4	NO	ALL	213827-5
	OBSOLETE	3	YES	ALL	213827-4
		2	YES	1-8, 10-19	213827-2
OBSOLETE	.368	2	YES	ALL	213827-1
	L	CONTACT FINISH	PERIPHERAL SEAL	SELECT LOADED IN POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 21MAY2003	TE Connectivity	
DIMENSIONS: INCHES		CHK S. HEADER 21MAY2003		
		APVD S. HEADER 21MAY2003	NAME RECEPTACLE ASSEMBLY, POSTED, REVERSE SEX, SERIES 1, 23-19, CPC	
		PRODUCT SPEC 108-10024		
MATERIAL -		APPLICATION SPEC 114-10038	SIZE A100779C=213827	
		FINISH -		
CUSTOMER DRAWING		WEIGHT -	RESTRICTED TO -	
		SCALE 3:1	SHEET 1 OF 2	
		REV P		



RECOMMENDED PC BOARD LAYOUT
 .125 MAX PANEL THICKNESS

4805 (3/13)