


NOTES:

1. 0.197 [5,0] MAX. PANEL THICKNESS
2. MATERIALS:
BODY - BRASS, NICKEL OR GOLD PLATED
TIP TERMINAL - BRASS, NICKEL PLATED
INSULATOR - ABS
NUT - BRASS, NICKEL OR GOLD PLATED
TOOTH WASHER - STEEL, NICKEL PLATED
BODY TERMINAL - BRASS, NICKEL PLATED
3. THIS PRODUCT IS RoHS COMPLIANT.

BPJ R 01 AU X
BULKHEAD PHONO JACK REAR MOUNT
RoHS COMPLIANT

PLATING:
AU = GOLD
BLANK = NICKEL

INSULATOR COLOR
01 = BLACK
02 = RED
03 = WHITE
04 = YELLOW
05 = BLUE
06 = GREEN



★ STAR SYMBOL DENOTES CRITICAL DIMENSION

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES
-TWO PLACE DECIMALS ± 0.01
-THREE PLACE DECIMALS ± 0.005
-ANGLES $\pm 1^\circ$
-ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.

2. FEATURES ON THE SAME CENTERLINE
MUST BE ALIGNED WITHIN ± 0.002

3. REMOVE ALL BURRS

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED
BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

SIZE	WIDTH	MULT	LBS/M	TEMPER
------	-------	------	-------	--------

FINISH	MATERIAL		
SPEC No.	SPEC No.		

FIRST USED ON		SCALE	
		2:1	

DATE DRAWN	BY	CHKD	APVD
------------	----	------	------

3-16-07	TJK	TJK	TJK
3-16-07		3-16-07	3-16-07

NAME	PART No.		
------	----------	--	--

RCA PHONO JACK
REAR MOUNT, RoHS

Switchcraft®

SHEET 1 OF 1

REV B

REV ECO NUMBER DATE BY APVD

REVISIONS

DO NOT SCALE DRAWING