




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		D	REVISED PER ECO-12-015665	26SEP12	KH	MZ




- 1 NYLON, UL 94V-0 RATED, BLACK.
- 2 STAINLESS STEEL.
- 3 BRASS.
- 4 CONTACT BODY: 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END. GOLD FLASH ON REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL. CONTACT POST: 2.54um [.000100] MIN TIN-LEAD OVER 1.27um [.000050] MIN NICKEL.
- 5 RECOMMENDED PC BOARD HOLE SIZE FOR CONTACT POST = 0.89±0.08 [.035±.003] DIA..
- 6 CONTACT BODY: 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END. GOLD FLASH ON REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL. CONTACT POST: 2.54um [.000100] MIN TIN OVER 1.27um [.000050] MIN NICKEL.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

7 OBSOLETE	6	YES	213855-4
	6	NO	213855-3
	4	YES	213855-2
	4	NO	213855-1
FINISH		THREADED INSERTS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.HARDY 01-03-95	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R.STONE 01-09-95				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME			
0 PLC ± -		PRODUCT SPEC	108-10024			
1 PLC ± -		APPLICATION SPEC	114-10038			
2 PLC ± 0.25 [.010]		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=213855	RESTRICTED TO -
3 PLC ± -		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 of 2	REV D	
4 PLC ± -						
ANGLES ± -						
FINISH -						
MATERIAL HOUSING: 1						
CONTACT SPRING: 2						
CONTACT BODY & POST: 3						

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
FT	0		-	SEE SHEET 1	-	-



RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
D.HARDY
01-03-95

CHK
R.STONE
01-09-95

APVD
-

PRODUCT SPEC
108-10024

APPLICATION SPEC
114-10038

WEIGHT
-

TE Connectivity

RECEPTACLE ASSEMBLY, POSTED,
STANDARD SEX, 17-16, CPC

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=213855

RESTRICTED TO
-

MATERIAL
HOUSING: 1

CONTACT SPRING: 2

CONTACT BODY & POST: 3

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.25 [.010]

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

CONTACT: 4

CUSTOMER DRAWING

SCALE
2:1

SHEET
2 OF 2

REV
D