

4

3

2

1

used for:

DIN 41651

B

4

13.9

POS.	B ±0.2	Part-N0.
10	17.30	140X10059X
14	22.40	140X10069X
16	24.90	140X10079X
20	30.00	140X10089X
26	37.60	140X10099X
34	47.80	140X10109X
40	55.40	140X10119X
50	68.10	140X10129X
60	80.80	140X10139X
64	85.85	140X10159X

Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	

NOTES:

1. INSULATORS: PBT GV, V0, UL 94, GREY RAL 7035
2. OPERATING TEMPERATURE RANGE: -55°C TO +125°C

tolerance



scale:

2:1

material:

SEE NOTES

title:

STRAIN RELIEF
10-64pos.

dwg no:

AutoCAD 2000

DIN-A

14K1A013

4

sh: 1/1

part no:

SEE TABLE

rev.	description	date	name
------	-------------	------	------

CONEC®

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND