







- SPECIFICATIONS
- Current Rating: 9A AC, DC
 - Voltage Rating: 600V AC, DC
 - Temperature Range: -25°C~+85°C
 - Contact Resistance: 20mΩ Max
 - Insulation Resistance: 1000MΩ Min
 - Withstanding Voltage: 1500V AC/minute
 - Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated



PCB LAYOUT

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制 图 DRAWING	H	Y	料号	版本	
			X.±0.25	X.±2°				PART NO.		REV.
			.X±0.20	.X±1°	审 核 CHECK	L P J		品 名 TITLE	55699双排弯针	页 次 SHEET
			.XX±0.15	.XX±0.5°	核 准 APPROVAL	L Z W		客户料号 CUST. NO.		1/1
			.XXX±0.10	.XXX±0.5°	单 位 UNITS	MM	比例 SCALE	深圳市富港科技有限公司		
										1:1