




RoHS



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material:Wafer PA66
PIN Brass Tin-plated

编 号	尺寸 (mm)		
	A	B	C
PHB-2*02AW	2.00	6.00	3.00
PHB-2*03AW	4.00	8.00	3.00
PHB-2*04AW	6.00	10.00	3.00
PHB-2*05AW	8.00	12.00	5.00
PHB-2*06AW	10.00	14.00	7.00
PHB-2*07AW	12.00	16.00	9.00
PHB-2*08AW	14.00	18.00	11.00
PHB-2*09AW	16.00	20.00	13.00
PHB-2*10AW	18.00	22.00	15.00
PHB-2*11AW	20.00	24.00	17.00
PHB-2*12AW	22.00	26.00	19.00
PHB-2*13AW	24.00	28.00	21.00
PHB-2*14AW	26.00	30.00	23.00
PHB-2*15AW	28.00	32.00	25.00
PHB-2*16AW	30.00	36.00	27.00
PHB-2*17AW	32.00	38.00	29.00
.....			
PHB-2*22AW	42.00	46.00	39.00

GENERAL TOLERANCE		制 图 DRAWING	H Y		料 号 PART NO.	PHB-2*NAW	版 本 REV.	A
X.±0.25	X.°±2°	审 核 CHECK	L P J		品 名 TITLE	PHB带扣弯针		
.X±0.20	.X°±1°							
.XX±0.15	.XX°±0.5°	核 准 APPROVAL	L G		浙江富港电子有限公司 ZHEJIANG FUGANG ELECTRONICS CO.,LTD			
.XXX±0.10	.XXX°±0.5°	单 位 UNITS						MM

浙江富港电子有限公司
ZHEJIANG FUGANG ELECTRONICS CO., LTD