





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-950006	2009/04/17	Jiang Jun Hua	Change Mark
C	LEN14C0387	2014/12/04	Vicky	Update Logo & Dimension



8	8	8	Gray	灰
7	7	7	Yellow	黃
6	6	6	Green	綠
5	5	5	White	白
4	4	4	Brown	棕
3	3	3	Blue	藍
2	2	2	Black	黑
1	1	1	Red	紅
Conn.1	Conn.2	Conn.3	Wire Color	



- Note:
- * (QC) Important Dimension.
 - * Waterproof Rate: IP66
 - * Connector: Nylon+GF, Black
 - * Pin: Copper Alloy, Gold Plated
 - * Lock Nut: Nylon+GF, Black
 - * O-Ring: EPDM, Black
 - * Wire Harness: UL1007 24AWG

UNIT:mm		TITLE	Standard T Adaptor Lock 8Pin FMM Conn FMM Pin	
TOLERANCE	±0.5 mm	SCALE	1:1	SIZE A4
		REV.	C	WC-REV. A.3
			(QC) Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	BA-080808-FMM-TL001	DRAWN BY	Vicky	DATE	2014-12-04
DWG NO	BA-080808-FMM-TL001	CHECKED BY	Sam	DATE	2014-12-04
CUSTOMER	ALTW	APPROVED BY	Rita	DATE	2014-12-04