


NOTES

1 PACKAGING QUANTITY: 5 PIECES PER BOX

2 MATERIAL: SEE TABLE

3 FINISH: VARNISH

4 VARNISH ON THE INSIDE NOT NECESSARY



PN 0-1 as shown

PN 0-4

Ordering Text
HA-K.16.SGD-LB.2.M20.Z

OBSELETE

1	-	Surface Mounted Housing-Side Entry	Aluminium	HC	Black	6	-
-	-	Cover	Aluminium	-	Grey	5	-
-	-	Profile Seal	Neoprene	-	Black	4	-
1	1	Side Clip	Steel	Zinc Plated	Blue	3	-
-	-	Surface Mounted Housing-Side Entry	Aluminium	-	Grey	2	-
-	1	Surface Mounted Housing-Side Entry	Aluminium	-	Grey	1	-

0-4	0-2	0-1	DESCRIPTION	MATERIAL	SURFACE	COLOR	ITEM NO.	REMARKS
-----	-----	-----	-------------	----------	---------	-------	----------	---------

DIMENSIONS:
DIMENSIONEN:
mm

0 PLC

1 PLC

2 PLC

3 PLC

ANGLES / WINKEL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN

n. ISO 8015

n. ISO 2768

n. DIN 16901

mH-E

140

MATERIAL

FINISH / OBERFLÄCHE / FARBE

DWN
P.BENNUR
3/2/2006

CHK
R.SRINIVAS
3/2/2006

APVD
T.SCHNURPFEIL
3/2/2006

PRODUCT SPEC.
PRODUKTSPEZ.

APPLICATION SPEC.
VERARBEITUNGSSPEZ.

WEIGHT
GEWICHT

TE Connectivity

SURFACE MOUNTED HOUSING, SIDE ENTRY
HA.16.SG/D-LB.2.M20.Z

SIZE
A3

CAGE CODE
00779

DRAWING NO.
ZEICHNUNGS-NR.
1106438

RESTRICTED TO
NUR FÜR

CUSTOMER DRAWING / KUNDENZEICHNUNG

SCALE
MASSSTAB
1:1

SHEET
BLATT
1

OF
VON
1

REV.
B2