







- SPECIFICATIONS
- Current Rating: 9A AC, DC
 - Voltage Rating: 600V AC, DC
 - Temperature Range: -25°C~+85°C
 - Contact Resistance: 20mΩ Max
 - Insulation Resistance: 1000MΩ Min
 - Withstanding Voltage: 1500V AC/minute
 - Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated



PCB LAYOUT

编 号	尺寸 (mm)	
	A	B
5569-2X01A		5.40
5569-2X02A	4.20	9.60
5569-2X03A	8.40	13.80
5569-2X04A	12.60	18.00
5569-2X05A	16.80	22.20
5569-2X06A	21.00	26.40
5569-2X07A	25.20	30.60
5569-2X08A	29.40	34.80
5569-2X09A	33.60	39.00
5569-2X10A	37.80	43.20
5569-2X11A	42.00	47.40
5569-2X12A	46.20	51.60

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制 图 DRAWING	H	Y	料号 PART NO.	5569-2xNA	版本 REV.	A	
			X.±0.25	X.±2°								
			.X±0.20	.X±1°	审 核 CHECK	L P J		品 名 TITLE	5569双排直针	页 次		
			.XX±0.15	.XX±0.5°	核 准 APPROVAL	L Z W		客户料号	WATER DIP TYPE	SHEET	1/1	
			.XXX±0.10	.XXX±0.5°	单 位 UNITS	MM	比例 SCALE	深圳市富港科技有限公司				
							1:1					