



REV.	ECN. NO.	APPD.
A		

NOTES:
 Current Rating:1.5AMP
 Contact Resistance:20mΩ max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ min
 Operation Temperature:-40℃ to +105℃

Contact Material:Brass
 Contact plating:Au or Sn Over Ni
 Insulator Material:PA6T+30%GF(UL94V-0)





Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information

MTP220-12XXM1

No.of Pins per
 Row: 01~40



Dimension antitheses list			
ITEM	B	D	W
Standard	4.00	0.50	6.50
Alternate			

X. ± 0.30	X.° ± 5°	UNITS mm	NAME(INTENDED USE)	MINTRON CO.,LTD.			
.X ± 0.20	.X° ± 2°	MAT'L					
.XX ± 0.10	.XX° ± 1°	FINISH	PART NO.(INTENDED USE)	TITLE: PH2.00 DUAL ROW SMT H=2.0			
.XXX ± 0.05	.XXX° ± 0.5°						
PIN HEADER CONNECTOR			APPD: SUNNY	DWG NO.: MTP220-12XXM1			
		Q'TY	CHKD: LISA				
			DR: ZOE 2006-11-28		SCALE	SHEET	REV.
					1 / 1	1 / 1	A