





PRODUCT SPECIFICATION

版本号
Version Number: _____

产品编码
PART Number: _____



- 一. 电气性能
1-1. 额定电压: 250V AC, DC
1-2. 额定电流: 2A
1-3. 接触电阻: 20mΩ MAX
1-4. 绝缘电阻: 1000MΩ MIN
二. 物流特征
2-1. 操作温度: -25℃~85℃
2-2. 焊接温度: +220℃, 10s max
三. 插拔力: 25mN

11	26.00	20.00	24.50				
10	24.00	18.00	22.50				
9	22.00	16.00	20.50				
8	20.00	14.00	18.50				
7	18.00	12.00	16.50				
6	16.00	10.00	14.50				
5	14.00	8.00	12.50				
4	12.00	6.00	10.50	14	32.00	26.00	30.50
3	10.00	4.00	8.50	13	30.00	24.00	28.50
2	8.00	2.00	6.50	12	28.00	22.00	26.50
POS.	DIM. A	DIM. B	DIM. C	POS.	DIM. A	DIM. B	DIM. C

③	定位片	2pcs	Copper alloy 黄铜镀锡	GENERAL TOLERANCES 一般公差				DRAW :	林加才	2016.06.01	名称 TITLE:	2.00 Pitch PH Connector	DRAW NAME:	
②	pin针	npes	Copper alloy 黄铜镀锡	DIM	TOL	DIM	DBG	DESIGN:	林加才	2016.06.01	SERIES:		PH2.0-A 贴片式连接器	
①	基座	1pcs	Material: High-temperature plastic, COLOR: NATURAL 材料: 耐高温 塑料 颜色: 本色 米黄	X. I	±0.35	X. I'	±2.00°	CHECK:	朱青峰	2016.06.01	P/N:		DRAW NO.	
NO.	PART NAME:	Q'TY	DESCRIPTION 类型	X. II	±0.35	X. II'	±1.00°	APPROVED	朱青峰	2016.06.01	REV.	1.00	SCALE	N/A
				X. III	±0.15	X. III'		CUSTOMER DRAWING 客户图纸					UNIT:	SHEET:
													mm	1/1