






REV.	ECN NO OR DESCRIPTION	REVISED	DATE

- NOTE: 1
1. ELECTRICAL CHARACTERISTICS:
- 1.1 CURRENT RATING: 0.5A MAX.
- 1.2 IMPEDANCE: 50OHM NOMINAL.
2. MECHANICAL CHARACTERISTICS:
- 2.1 OPERATING TEMP. -40°~90°
- 2.2 VEW R UP TO 3GHz: 1.3MAX.
- 3GHz TO 6GHz: 1.4MAX.
- 2.3 DURABILITY: 30CYCLES



UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:	ANGLES:
X :±0.35	X :±2°
X.X :±0.25	X.X :±1°
X.XX :±0.15	



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	RF BOARD END CONNECTOR FIRST GENERATION			
DWN	xiong	PART NO. SP-IPEX-001A		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
CUSTOMER COPY				