







4~24P	0.10
25~30P	0.12



适用扁平线 (Applicable Flat Cable)



适用线路板 (PCB LAYOUT)

技术指标:

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
- 温度范围: -25° C~85° C.
- 额定电压: 50V, AC/DC(等效).
- 接触电阻: ≤0.03Ω.
- 绝缘电阻: ≥500MΩ

REV.	ECN NO OR DESCRIPTION	REVISED	DATE

序号	品名	材质
①	0.5掀盖胶芯 (H1.5)	LCP UL94V-0 本色
②	0.5掀盖端子 (H1.5)	铜合金/表面镀锡
③	0.5掀盖后盖 (H1.5)	LCP UL94V-0 黑色
④	0.5掀盖焊片 (H1.5)	铜合金/表面镀锡

TABLE:

CSG PART NO.	PIN数	DIM.A	DIM.B	DIM.C
HB-FPC-10FGXJ-H154P	4PIN	3.00	8.70	5.03
HB-FPC-10FGXJ-H155P	5PIN	4.00	9.70	6.03
HB-FPC-10FGXJ-H156P	6PIN	5.00	10.70	7.03
HB-FPC-10FGXJ-H157P	7PIN	6.00	11.70	8.03
HB-FPC-10FGXJ-H158P	8PIN	7.00	12.70	9.03
HB-FPC-10FGXJ-H159P	9PIN	8.00	13.70	10.03
HB-FPC-10FGXJ-H1510P	10PIN	9.00	14.70	11.03
HB-FPC-10FGXJ-H1512P	12PIN	11.00	16.70	13.03
HB-FPC-10FGXJ-H1514P	14PIN	13.00	18.70	15.03
HB-FPC-10FGXJ-H1516P	16PIN	15.00	20.70	17.03
HB-FPC-10FGXJ-H1517P	17PIN	16.00	21.70	18.03
HB-FPC-10FGXJ-H1518P	18PIN	17.00	22.70	19.03
HB-FPC-10FGXJ-H1520P	20PIN	19.00	24.70	21.03
HB-FPC-10FGXJ-H1522P	22PIN	21.00	26.70	23.03
HB-FPC-10FGXJ-H1524P	24PIN	23.00	28.70	25.03
HB-FPC-10FGXJ-H1526P	26PIN	25.00	30.70	27.03
HB-FPC-10FGXJ-H1527P	27PIN	26.00	31.70	28.03
HB-FPC-10FGXJ-H1528P	28PIN	27.00	32.70	29.03
HB-FPC-10FGXJ-H1530P	30PIN	29.00	34.70	31.03

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:	ANGLES:
X :±0.30	X :±2°
X.X :±0.20	X.X :±1°
X.XX :±0.10	



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	FPC 1.0Pitch 1.5H下接掀盖式connector			
DWN	xiong	PART NO. HB-FPC-10FGXJ-H15NP		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
CUSTOMER COPY				