


RoHS

MAPX

MODIFICATION

DRW

DATE



Material

Insulator: PBT UL 94V0.

Contact: brass, gold/Tin plated.

Shell: cold roller steel, Nickel plated.





Environmental

Operating temperature: $-55^\circ \sim +105^\circ$.

Electrical

Contact current rating: 5Amp.

Dielectric withstanding volt: AC 1000V/min.R.M.S.

Insulation resistance: $>5000\text{M OHM min. at } 500\text{V DC}$.Contact resistance: 25M OHM Max .

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	± 0.35	X.	$\pm 5^\circ$
.X	± 0.30	.X	$\pm 2^\circ$
.XX	± 0.25	.XX	$\pm 1^\circ$
.XXX	± 0.05	.XXX	$\pm 0.5^\circ$

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.单位
UNITS

MM

制图
DRAWING

L-S-S

产品料号
PRODUCT PART NO.

920-H0108021Y00103

比例
SCALE

1:1

审核
CHKD

G-Z-F

产品名称
PRODUCT NO.

DP-180度9PIN公头PBT黑胶半金镀合(鱼叉锁螺丝)

日期
DATE

2021-03-10

核准
APPD

黄国荣

角法
VIEW版本
VER

A0