

RoHS

NOTE:

1. MATERIAL:

USB 2.0 HOUSING: HIGH TEMPERATURE THERMOPLASTIC , GLASS
FIBER FILLED, UL94V-0, COLOR : BLACK.

USB 3.0 HOUSING: HIGH TEMPERATURE THERMOPLASTIC , GLASS
FIBER FILLED, UL94V-0, COLOR : BLUE.

CONTACTS: COPPER ALLOY

SHELL: MEATL ALLOY

REAR SHELL: SUS

2. FINISH:

CONTACTS: GOLD(SEE TABLE) PLATING IN CONTACT AREA,






100 μ " MIN. MATTE-TIN PLATING ON SOLDER TAILS.

50 μ " MIN. NICKEL UNDERPLATING OVER ALL.

SHELL: 100 μ " MIN. NICKEL PLATING.

ISOLATED:SHELL: 100 μ " MIN. NICKEL PLATED.

3. WAVE SOLDER CAPABLE TO 265°C



REFERENCE P.C.B LAYOUT

产品图

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

公差一览表			单位			制图			产品料号		
TOLERANCE UNLESS OTHERWISE			UNITS			DRAWING			PRODUCT PART NO.		
X.	±0.35	X.	±5.°	比例	1:1	审核	G-Z-F	产品名称	USB A TYPE 3.0 TWO LAYER	版本	A0
.XX	±0.20	.XX	±1.°	日期	2021-03-10	核准	黄国荣	角法			
.XXX	±0.05	.XXX	±0.5°	DATE		APD		角法			

