




技术要求


1:外观要求

- 1—1. 插针表面光洁、无损伤、锈蚀等缺陷。
1—2. 基座表面无脏污、飞边、排气不良等缺陷。

2:电气性能:

- 2—1. 额定电流:1.0A
2—2. 额定电压:50V
2—3. 耐电压:500V
2—4. 接触电阻:≤20mΩ
2—5. 绝缘电阻:≥100mΩ

3:工作温度:—25℃~+85℃



P.C.B Layout

Part No	Pin	A	B	C
WAFER-SHB1.0-2PWB	2	1.00	2.60	4.50
WAFER-SHB1.0-3PWB	3	2.00	3.60	5.50
WAFER-SHB1.0-4PWB	4	3.00	4.60	6.50
WAFER-SHB1.0-5PWB	5	4.00	5.60	7.50
WAFER-SHB1.0-6PWB	6	5.00	6.60	8.50
WAFER-SHB1.0-7PWB	7	6.00	7.60	9.50
WAFER-SHB1.0-8PWB	8	7.00	8.60	10.50
WAFER-SHB1.0-9PWB	9	8.00	9.60	11.50
WAFER-SHB1.0-10PWB	10	9.00	10.60	12.50
WAFER-SHB1.0-11PWB	11	10.00	11.60	13.50
WAFER-SHB1.0-12PWB	12	11.00	12.60	14.40
WAFER-SHB1.0-13PWB	13	12.00	13.60	15.50
WAFER-SHB1.0-14PWB	14	13.00	14.60	16.50
WAFER-SHB1.0-15PWB	15	14.00	15.60	17.50
WAFER-SHB1.0-16PWB	16	15.00	16.60	18.50

序号	材料名称	数量	材质	镀涂
1	卧贴针	N	磷铜	高温亮锡
2	塑件	1	LCP	/
3	焊片	2	磷铜	高温亮锡
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		 TITLE: SH1.0-4P-卧贴-带扣		
DECIMALS:	ANGLES:	PAR	WAFER-SHB1.0-NPWB	
3<:±0.1		DWN	Lucas	
>3<10:±0.15		CHKD	Ethan	
>10<20:±0.2		APVD	Jacob	
CUSTOMER COPY		SCALE:1:1	UNIT:MM	
		SIZE:A4	SHEET:1F1	REV:A