

修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
AO		NEW DWG		2023-09-25




◆ SPECIFICATIONS

- Current rating: 2.0A AC, DC
- Voltage rating: 250V AC,DC
- Temperature range: -25°C ~ +85°C
- Insulation resistance: 500MΩ Min.
- Withstanding voltage: 500V AC/ minute.
- Contact resistance: 20m Ω Max.


Material:

Housing: LCP UL94V-0 , BEIGE
Contacts: Brass/ MATTE Sn-plated
Solder Tabs: Brass/ MATTE Sn-plated
Suitable: HDGC1508HA-2xXP series Dual Row Housing

PIN	尺寸 mm		
	A	B	C
2x2P	1.50	3.72	6.74
2x3P	3.00	5.22	8.24
2x4P	4.50	6.72	9.74
2x5P	6.00	8.22	11.24
2x6P	7.50	9.72	12.74
2x7P	9.00	11.22	14.24
2x8P	10.50	12.72	15.74
2x9P	12.00	14.22	17.24
2x10P	13.50	15.72	18.74
2x11P	15.00	17.22	20.24
2x12P	16.50	18.72	21.74
2x13P	18.00	20.22	23.24
2x14P	19.50	21.72	24.74
2x15P	21.00	23.22	26.24
2x16P	22.50	24.72	27.74
2x17P	24.00	26.22	29.24
2x18P	25.50	27.72	30.74
2x19P	27.00	29.22	32.24
2x20P	28.50	30.72	33.74



SECTION A—A



P.C.B LAYOUT
TOLERANCE: ± 0.05



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-27129737 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		 	TITLE: 产品名称: MXH1.5 双排带扣立贴			
X.X	± 0.30	X.X'	$\pm 3'$	APPD: 核准: 谢亮	PART NO: 产品编号: HDGC1502WVA-S-2xXP-2	
X.XX	± 0.30	X.XX'	$\pm 2'$	CHECK: 校对: 王建业	DATE	SCALE
X.XXX	± 0.10	X.XXX'	$\pm 1'$	DRAW: 绘图: 黄艳兰	UNIT	CODE NUMBER
				2023-09-25	1:1	mm
				A001		