






Circuit 1

2-3 Pin
Without Sticking PointRECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05 

P/N	Dimensions(mm)		
	A	B	C
WAFER-ACH1.2-2PWB	1.20	4.20	2.64
WAFER-ACH1.2-3PWB	2.40	5.40	3.84



3D View

Specification

Voltage Rating : 50V AC/DC

Current Rating : 2A AC/DC

Withstanding Voltage : 500V AC /minute

Insulation Resistance : $\geq 100M\Omega$ minTemperature Range : -40°C to $+105^{\circ}\text{C}$ Contact Resistance : $\leq 20m\Omega$ After Environmental Testing: $\leq 40m\Omega$

Suitable Wire/Cable:AWG #28 to #30,

OD:0.8mm max

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:1.2mm(.047") pitch PCB Header/Wafer R/A SMD/SMT Connector
			PAR WAFER-ACH1.2-NPWB
DECIMALS:	ANGLES:		DWN Lucas
.X:±0.30	±3°		CHKD Ethan
.XX:±0.20			APVD Jacob
.XXX:±0.10		CUSTOMER COPY	
		SIZE:A4	SHEET:1F1
			REV:A