


标记	处数	更改前内容	更改后内容	签名	年.月.日



孔位	A	B	C
2X5	12.0	8.0	10.6
2X6	14.0	10.0	12.6
2X7	16.0	12.0	14.6
2X8	18.0	14.0	16.6
2X9	20.0	16.0	18.6
2X10	22.0	18.0	20.6
2X11	24.0	20.0	22.6
2X12	26.0	22.0	24.6
2X13	28.0	24.0	26.6
2X14	30.0	26.0	28.6
2X15	32.0	28.0	30.6
2X16	34.0	30.0	32.6
2X17	36.0	32.0	34.6
2X18	38.0	34.0	36.6
2X19	40.0	36.0	38.6
2X20	42.0	38.0	40.6

使用温度范围 (Ambient temperature Range): $-25^{\circ}\sim+85^{\circ}$

适用线规 (Applicable Wires):AWG 28#~22#

额定电压 (Voltage rating):250V AC,DC

额定电流 (Current rating):3A

接触电阻 Contact Resistance): $\leq 0.02\Omega$

绝缘电阻 (Insulation Resistance): $\geq 1000M\Omega$

耐压 (Withstand Voltage):1000V/min

材料 (Material)

1.基座: PA66 94V-(0)

范围	>0-3	>3-18	>18-45	>45-100
公差	± 0.15	± 0.2	± 0.3	± 0.5

未注公差		材料	PA66 94V- (0)or ul			
尺寸范围	公差	比例	1:1	设计/日期	审核/日期	批准/日期
>20	±0.3	版次				
10-20	±0.25	重量		第1页 共1页	初始日期	2021-08-08
3-10	±0.2	浙江温达电子有限公司 ZHEJIANG WENDA ELECTRONICS CO.,LTD				
<3	±0.1					